


Dustpan Fitting Instructions CVS:

- 1) The flip flop door is spring driven and factory adjusted. Do not tighten spring screw.
- 2) To re-adjust flip flop door finger tight screws and back off ½ a turn.
- 3) To connect dustpan to 2" standard fitting, a tight layer of tape may be required.
- 4) To take screw caps out, pull from 'inside edge first'. 2 x special pieces of double side tape are provided to further secure screw caps.
- 5) To use KitVac adaptor provided, then connects to 38mm ID (1-1/2" ID) Standard vacuum hose cut to your required length. Then cut 2" pipe piece (sleeve say 40mm/1 ½" long) which will go over the other end – Then you have a low cost flexible pipe solution that will connect back into your main 2" line. Ensure all joints are secured by tape.

Dustpan Dimensions are;



Dustpan Template cut out.

